



BDBSCS1S1S1, Flex Rated Stud Style Power Distribution Block

By Burndy
Catalog # [BDBSCS1S1S1](#)

Aluminum Power Distribution Block, 1 Pole, Run: 1/4" Stud, Tap: 1/4" Stud, 310 Amp/Pole

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Specifications

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance	CM
Status	



Configuration

Connector Type	Power Distribution Block
----------------	--------------------------

Dimensions

Height	3.03 in
Length	3.48 in

General

Material	Aluminum
UPC	621945481664

Logistics

Minimum Pack Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)