



BDBSHCCOVER, Power Distribution Block Cover

By Burndy
Catalog # [BDBSHCCOVER](#)

Polycarbonate Safety Cover for Power Distribution Blocks, Black, Small Size



Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

Application

Industrial control feeder, HVAC system and wire ways

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	---

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Height mm	16 mm
Dimension - Height inch	0.63 in
Dimension - Width mm	25 mm
Dimension - Width inch	0.97 in
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.45 in

General

Plated	Y
Trade Name	VERSIPOLE™
Sub Brand	VERSI-POLE
UPC	781810646144
Type	BDB
Insulation	Y
Material	Polycarbonate
Plating Type	Unplated
UPC 12 Digit	781810646144
UPC 14 Digit GTIN	00781810646144

Logistics

Minimum Pack Quantity	1
Pallet Quantity	13125
Carton Quantity	200

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)