



ES6W6W, Insulated Aluminum Service Entrance Compression Sleeve

By Burndy
Catalog # [ES6W6W](#)

Insulated AL service entrance compression sleeve



Features

- Pre-insulated service entrance compression connector
- Polyethylene caps prevent dirt from accumulating in barrel, grip cable for easy two-hand installation, seal out moisture
- Connector is anchored to jacket assuring the connector is under the die when crimping
- Prefilled with joint compound and stripealed to limit oxidation and increase life of the connection

Application

For Insulated Combinations Of Copper, Aluminum, ACSR Compressed Conductors And In Overhead Distribution

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A Range	8 AWG-6 AWG
Conductor - Copper Solid Size A	6 AWG
Conductor - Copper Solid Size B	• 8 AWG • 7 AWG • 6 AWG
Conductor - Copper Solid Size A Range	6 AWG
Conductor - Copper Solid Size B Range	6 AWG
Conductor - AL Str Size A Range	8 AWG-6 AWG
Conductor - AL Str Size B Range	8 AWG-6 AWG

Conductor - Copper Str Size B Range 6 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	70 mm
Dimension - Outside Diameter inch	.75 in
Dimension - Length Overall inch	2.75 in

General

Plated	Y
Insulation Type	Nylon
Trade Name	INSULINK™
Sub Brand	INSULINK
Die Index	BG or 5/8
UPC	781810142905
Color Code - Side B	Green
Color Code - Side A	Green
Type	Insulated Service Entrance Connectors
Prefilled Oxide Inhibitor	Y
Insulation	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810142905
UPC 14 Digit GTIN	00781810142905

Logistics

Pallet Quantity	24000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)