



FCB644N, Substation - Copper Tap Adapter

By Burndy
Catalog # [FCB644N](#)

Transformer tap adapter, Tin plated, For Cu & Al

Features

- Cast in one piece copper alloy
- Transformer tap adapter designed to accommodate NEMA drilled terminals taps from a single secondary transformer outlet
- Tin-Plated

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
----------------	---

Configuration

Physical Attribute - Number of Holes	4
Connector Type	T-Connector

Dimensions

Dimension - Pin Diameter inch	.75 in
Dimension - Pin Diameter fraction	3/4 in
Package Height	0.000 in
Dimension - Height mm	146.1 mm
Dimension - Height inch	5.75 in
Dimension - Height fraction	5-3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	2.75 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.00 in

General

Plated	Y
Sub Brand	TAP ADAPTER
UPC	781810188019
Type	T-Connector
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810188019
UPC 14 Digit GTIN	00781810188019

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)