



BONDIT Wall Mount Intersystem Bonding Connector, #14-#2 AWG

By Burndy
Catalog # [BDTIBB](#)

BONDIT® Wall Mount Intersystem Bonding Connector, #14 - #2 AWG, Meets NEC 250.94

Features

- Meets Intersystem Bonding Requirements: NEC 250.94
- Provides an easy to access grounding point for utilities such as telecom and cable
- Easy to install
- Tin-plated connector body provides long-lasting corrosion resistance
- UL467 Listed for the US and Canadian Markets
- Stainless Steel Set Screws
- Accepts main ground wire (#2 to #6), up to 4 intersystem wire (#4 to #14)
- Supplied with a durable cover, easily secured over connector body
- Approved for use with solid stranded conductors

Application

Used to tying all of the system grounds together in one location

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
EU RoHS Indicator	Under Review

UL Listed	Yes
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
Dimension - Height inch	0.91 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Trade Name	BONDIT®
Sub Brand	BONDIT
UPC	781810504017
Type	BDT
UPC 12 Digit	781810504017
UPC 14 Digit GTIN	00781810504017

Logistics

Pallet Quantity	3360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)