



BIBD2502, 2-Sided Two Cond. Clear Ins. MultiTap

By Burndy
Catalog # [BIBD2502](#)

#10 AWG - 250 kcmil, 2 Ports, Double-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	8 AWG-250 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG



- 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250 kcmil
- Conductor Size 10 AWG-250 KCMIL
- Conductor Type
- AL C Str-Size
 - CU C Str-Size
- Conductor - Copper Str Size Range 10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	54.1 mm
Dimension - Height inch	2.13 in
Dimension - Height fraction	2.125 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	52 mm
Dimension - Width fraction	2-16/25 in
Dimension - Width mm	67 mm
Dimension - Width inch	2.64 in
Dimension - Length Overall inch	2.03 in

Force Related

Installation Torque Recommended in-lb	125
---------------------------------------	-----

General

Product Family	MECHANICAL
Insulation Type	Plastisol

Trade Name	UNITAP™	UPC 14 Digit GTIN	00781810224052
Material - Hardware	Aluminum	Logistics	
Insulation	Y	Minimum Pack Quantity	1
Physical Attribute - Screw Type	Allen	Pallet Quantity	2304
Plated	No	Carton Quantity	24
Sub Brand	UNITAP	Operational	
Product Type	Run/Tap	Temperature Rating	194
UPC	781810224052	Product Assets	
Type	BIBD, Multi-Port	Catalog [English]	
Hex Key	5/16	Catalog [English]	
Material	Aluminum		
Plating Type	Unplated		
UPC 12 Digit	781810224052		

