



## BIBD3508MT, 2-Sided Mounted Eight Cond. Clear Ins. MultiTap

By Burndy

Catalog # [BIBD3508MT](#)

#10 AWG - 350 kcmil, 8 Port, Double-sided Entry, Al/Cu Rated, Mountable, Clear Plastisol allows visual confirmation conductor is properly inserted

### Features


- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

### Specifications

|                                         |       |
|-----------------------------------------|-------|
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Certification - ETL                     | No    |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | CM    |
| Certification - UL Listed Direct Burial | No    |
| UL Listed                               | Yes   |
| Certification - CSA Approved            | Yes   |

### Conductor

|                               |                                                                                                                                                                                                                                                                                                                     |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size       | <ul style="list-style-type: none"><li>• 8 AWG</li><li>• 6 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0 AWG</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 266 kcmil</li><li>• 300 kcmil</li><li>• 336 kcmil</li><li>• 350 kcmil</li></ul> |
| Conductor - AL Str Size Range | 8 AWG-350 kcmil                                                                                                                                                                                                                                                                                                     |
| Conductor - Copper Str Size   | <ul style="list-style-type: none"><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li></ul>                                                                                                                                                                                                            |



- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil
- 300 kcmil
- 350 kcmil

|                                   |                                                                                         |
|-----------------------------------|-----------------------------------------------------------------------------------------|
| Conductor Size                    | 10 AWG-350 KCMIL                                                                        |
| Conductor Type                    | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul> |
| Conductor - Copper Str Size Range | 10 AWG - 350 kcmil                                                                      |

### Configuration

|                                       |           |
|---------------------------------------|-----------|
| Physical Attribute - Number of Screws | 10        |
| Number Of Ports                       | 8         |
| Connector Type                        | Multi Tap |

### Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 66.8 mm   |
| Dimension - Height inch         | 2.63 in   |
| Dimension - Height fraction     | 2.625 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 241 mm    |
| Dimension - Width mm            | 76 mm     |
| Dimension - Width inch          | 3.00 in   |
| Dimension - Length Overall inch | 9.50 in   |

### General

|                 |           |
|-----------------|-----------|
| Insulation Type | Plastisol |
|-----------------|-----------|

|                                 |                |
|---------------------------------|----------------|
| Trade Name                      | UNITAP™        |
| Material - Hardware             | Aluminum       |
| Insulation                      | Y              |
| Physical Attribute - Screw Type | Allen          |
| Plated                          | N              |
| UPC                             | 781810253359   |
| Hex Key                         | 5/16           |
| Material                        | Aluminum       |
| Plating Type                    | Unplated       |
| UPC 12 Digit                    | 781810253359   |
| UPC 14 Digit GTIN               | 00781810253359 |

Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 1  |
| Pallet Quantity       | 1  |
| Carton Quantity       | 20 |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)



A Hubbell brand