



FD655C6SV, Substation - Copper Stud Connector

By Burndy
Catalog # [FD655C6SV](#)

Copper Stud Connectors

Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerlive of stud
- Pad is finished on both sides with 4-hole NEMA drilling
- Please contact factory for other sizes, combinations, plating variants and availability

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Physical Attribute - Pad Configuration	3x3 - 4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.125 in
Dimension - Pin Diameter fraction	1-1/8 in
Dimension - Pad Width inch	3.00 in
Dimension - Height mm	0 mm
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	1-3/4 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	147 mm
Dimension - B Length inch	1.75 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12
Dimension - Length Overall inch	5.80 in

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810243169
Type	Studs
Material	Copper Alloy
Plating Type	Silver
UPC 12 Digit	781810243169
UPC 14 Digit GTIN	00781810243169

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)