



FD655D6U, Substation - Copper Stud Connector, 4-Hole Pad, 1-1/8" Stud to NEMA Pad

By Burndy
Catalog # [FD655D6U](#)

Copper Stud Connector to 4 Hole Pad, 1-1/8 IN Stud to 4 Hole NEMA Pad, 6.86 IN L

Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Physical Attribute - Pad Configuration	4x4 - undrilled
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.125 in
-------------------------------	----------

Dimension - Pin Diameter fraction	1-1/8 in
Dimension - Pad Width inch	4.00 in
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	1-3/4 in
Dimension - Width mm	101.6 mm
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	174 mm
Dimension - B Length inch	1.75 in
Dimension - D inch	4.25 in
Dimension - N inch	1.13 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12
Dimension - Length Overall inch	6.86 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810221891
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810221891
UPC 14 Digit GTIN	00781810221891

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)