

BIBS35014, 14-Cond. Clear Ins. Multi-Tap

By Burndy
Catalog # [BIBS35014](#)

#10 AWG - 350 kcmil, 14 Ports, Single-sided Entry, Al/Cu Rated, Clear Plastisol allows visual confirmation conductor is properly inserted



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	10 AWG-350 KCMIL
Conductor - AL Str Size Range	10 AWG - 350 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 350 kcmil

Configuration

Physical Attribute - Number of Screws	10
Number Of Ports	14
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	64 mm
Dimension - Height inch	2.50 in
Package Weight	0.000 lb.
Dimension - Width mm	59 mm
Dimension - Width inch	2.32 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	334 mm
Dimension - Length Overall inch	13.14 in

General

Physical Attribute - Screw Type	Allen
Plated	N
Insulation Type	Plastisol
Trade Name	UNITAP™
UPC	781810233023
Insulation	Y
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810233023
UPC 14 Digit GTIN	00781810233023

Logistics

Minimum Pack Quantity	5
Pallet Quantity	600
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)