



FD675D8T0, Substation - Copper Stud Connector

By Burndy
Catalog # [FD675D8T0](#)

Copper Stud Connectors

Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Conductor - Connection Stud to Pad
Combination

Configuration

Physical Attribute - Pad In-line
Orientation
Physical Attribute - Pad 4x4 - 4 holes
Configuration
Physical Attribute - Number of 4
Holes
Connector Type Stud Connector

Dimensions

Dimension - Pin Diameter inch 1.750 in
Dimension - Pin Diameter 1-3/4 in
fraction
Dimension - Pad Width inch 4.00 in

Package Height 0.000 in
Dimension - Height mm 0 mm
Dimension - Bolt Size fraction 1/2
Package Weight 0.000 lb.
Package Length 0.000 in
Dimension - F Width Center to 1.75 in
Center inch
Package Width 0.000 in
Dimension - L Length Overall 188 mm
mm
Dimension - B Length inch 2.18 in
Dimension - D inch 4.00 in
Dimension - N inch 1.12 in
Dimension - Thread Size 1/2
Dimension - Length Overall 7.39 in
inch

General

Plated N
Material - Hardware DURIUM™ Silicon Bronze
UPC 781810348994
Type Studs
Material Copper Alloy
Plating Type Unplated
UPC 12 Digit 781810348994
UPC 14 Digit GTIN 00781810348994

Logistics

Minimum Pack Quantity 1
Pallet Quantity 1
Carton Quantity 1

Product Assets

[Catalog \[English\]](#)