



FD67C6W, Substation - Copper Stud Connector

By Burndy
Catalog # [FD67C6W](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	1.500 in
Dimension - Pin Diameter fraction	1-1/2 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810077719
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810077719
UPC 14 Digit GTIN	00781810077719

Logistics

Minimum Pack Quantity	1
Pallet Quantity	108
Carton Quantity	3

Product Assets

[Catalog \[English\]](#)