



BISR2, Clear Insulated Splice Reducer, #14-2 AWG

By Burndy
Catalog # [BISR2](#)

Aluminum UNITAP In-Line Splice Reducer, Clear Insulation, #14 - 2 AWG, AL9CU

Features

- Type BISR In-Line Splice/Reducers are easily installed on code conductor
- UL486B Listed, Dual rated AL9CU for any stranded copper or stranded aluminum applications

Application

For Indoor Use Only

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Size Range	14 AWG - 2 AWG
Conductor - Copper Str Size	• #14 • 12 AWG • 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2
Conductor Size	14-2 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG - 2 AWG



Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	In-Line

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	31 mm
Dimension - Height inch	1.22 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60 mm
Dimension - Width mm	19 mm
Dimension - Width inch	0.75 in
Dimension - Length Overall inch	2.38 in

Force Related

Installation Torque Recommended in-lb	100 in-lb
---------------------------------------	-----------

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP
Product Type	Splice Reducer
UPC	781810225196
Type	BISR, In-Line
Hex Key	5/32 in
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810225196
UPC 14 Digit GTIN	00781810225196

Logistics

Minimum Pack Quantity 1
Pallet Quantity 9600
Carton Quantity 100

Temperature Rating 90 °C

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)

Operational



A Hubbell brand