



FD67D8, Substation - Copper Stud Connector

By Burndy
Catalog # FD67D8

Cast Copper Alloy Stud Connector, 1-1/2"-12 Stud, 4 Pad holes, 7.3 in Length, Stud to Flat Bar

Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection	Stud to Pad
Combination	

Configuration

Connector Type	Stud Connector
----------------	----------------

Current

Amperage Rating	1450 A
-----------------	--------

Dimensions

Dimension - Pin Diameter inch	1.500 in
-------------------------------	----------

Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pad Width inch	4.00 in
Package Height	6.13 in
Dimension - Height mm	0 mm
Package Weight	19.52 lb.
Package Length	9.38 in
Package Width	7.44 in
Dimension - L Length Overall mm	185 mm
Dimension - Thread Size	1/2
Dimension - Bolt Size fraction	1/2
Dimension - B Length fraction	2-9/50 in
Dimension - B Length inch	2.18 in
Dimension - D inch	4.00 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	7.30 in

General

Material - Hardware	DURIUM™ Silicon Bronze
Plated	No
Sub Brand	STUD CONNECTOR
Product Type	Mechanical
UPC	781810003589
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810003589
UPC 14 Digit GTIN	00781810003589

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)