



BISR250, Clear Insulated Splice Reducer, #10 AWG-250 kcmil

By Burndy
Catalog # [BISR250](#)

Aluminum UNITAP In-Line Splice Reducer, Clear Insulation, #10 AWG - 250 kcmil

Features

- Type BISR In-Line Splice/Reducers are easily installed on code conductor
- UL486B Listed, Dual rated AL9CU for any stranded copper or stranded aluminum applications

Application

For Indoor Use Only

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor - Copper Str Size	• #10 • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG



- 1 AWG
 - 1/0
 - 2/0 AWG
 - 3/0 AWG
 - 4/0 AWG
 - 250
- 10 AWG-250 KCMIL
- AL C Str-Size
 - CU C Str-Size

Conductor Size	10 AWG-250 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 250 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	In-Line

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	53 mm
Dimension - Height inch	2.1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	102 mm
Dimension - Width mm	30 mm
Dimension - Width inch	1.19 in
Dimension - Length Overall inch	4.01 in

Force Related

Installation Torque Recommended	275 in-lb in-lb
---------------------------------	--------------------

General

Product Family	MECHANICAL
Insulation Type	Plastisol
Trade Name	UNITAP™
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	No
Sub Brand	UNITAP

Product Type	Splice Reducer	Minimum Pack Quantity	1
UPC	781810134108	Pallet Quantity	3240
Type	BISR, In-Line	Carton Quantity	90
Hex Key	5/16 in		
Material	Aluminum	Operational	
Plating Type	Unplated	Temperature Rating	90 °C
UPC 12 Digit	781810134108		
UPC 14 Digit GTIN	00781810134108	Product Assets	

Logistics

[Catalog \[English\]](#)
[Catalog \[English\]](#)



A Hubbell brand