



BISR2FX, Flex Rated Clear Insulated Splice Reducer

By Burndy
Catalog # [BISR2FX](#)

Aluminum UNITAP, In-Line Splice Reducer, #14-#2 Class B & C,
#14-#2 Class G,H,I,K, DLO, 2 Port



Features

- Type BISR-FX In-Line Splice/Reducers for Code and Flex conductor are listed to UL486A-B, CSA Certified to C22.2, No. 65, and AL9CU dual rated
- Range taking designs reduce inventory needs
- Screw Port and Conductor Port caps provide protection against contamination and accidental contact of energized parts
- Caps are color coordinated to quickly identify maximum conductor size
- Screw Port caps display recommended installation torque values for quick and easy reference
- Conductor Port caps show accommodated wire range and class

Application

Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors

Specifications

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Buy American Compliant	Under Review
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	14- 2 Str
Conductor Size	14-2 AWG
Conductor - Copper Flex G Size Range	14 - 2 Str
Conductor - Copper Flex K Size Range	14- 2 Str
Conductor Type	• AL C Str-Size • CU C Str-Size • CU C Flex-Size
Conductor - Copper Str Size Range	14 AWG - 2 AWG
Conductor - Copper Flex H Size Range	14- 2 Str

Conductor - Copper Flex I Size 14- 2 Str
Range

Configuration

Number Of Ports	2
Connector Type	In-Line

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	31 mm
Dimension - Height inch	1.22 in
Package Weight	0.000 lb.
Dimension - Width mm	19.05 mm
Dimension - Width inch	0.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60.45 mm
Dimension - Length Overall inch	2.38 in

Force Related

Installation Torque Recommended in-lb	100 in-lb
---------------------------------------	-----------

General

Plated	Y
Color Code	Brown
Insulation Type	Plastisol
Trade Name	UNITAP™
Sub Brand	UNITAP
UPC	621945439962
Type	BISR,Multi-Port
Insulation	Y
Hex Key	5/32 in
Material	Aluminum
Plating Type	Tin Plated Aluminum
UPC 12 Digit	621945439962
UPC 14 Digit GTIN	00621945439962

Logistics

Minimum Pack Quantity 1
Pallet Quantity 9600
Carton Quantity 100

Temperature Rating 135 °C

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)

Operational



A Hubbell brand