



BIT750, 1-Side, 2-Cond. Clear Insulated MultiTap

By Burndy
Catalog # [BIT750](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 2 AWG-750 kcmil, Al/Cu Rated



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size Range	2 AWG - 750 kcmil
Conductor Size	2 AWG-750 KCMIL
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 AWG - 750 kcmil

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	73 mm
Dimension - Width fraction	2-7/10 in
Dimension - Width mm	69 mm
Dimension - Width inch	2.70 in
Dimension - Length Overall inch	2.87 in

General

Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
Insulation	Y
Physical Attribute - Screw Type	Allen
Plated	N
Sub Brand	UNITAP
UPC	781810233139
Type	BIT
Hex Key	3/8 in
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810233139
UPC 14 Digit GTIN	00781810233139

Logistics

Pallet Quantity	1188
Carton Quantity	33

Operational

Temperature Rating	90°C
--------------------	------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)