



FD67T1212, Substation - Copper Stud Connector

By Burndy
Catalog # [FD67T1212](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.500 in
Dimension - Pad Width inch	2.00 in
Dimension - Height mm	0 mm
Dimension - Bolt Size fraction	3/8
Dimension - L Length Overall mm	108 mm
Dimension - D inch	2.00 in
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12
Dimension - Length Overall inch	4.25 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945010475
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945010475
UPC 14 Digit GTIN	00621945010475

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)