

BITO4FX, Opp. Side, Flex, 2-Cond. Clear Ins, MultiTap

By Burndy
Catalog # [BITO4FX](#)



Aluminum UNITAP, Tap - Opposite Side Entry, #14-#4 Class B & C, #14-#6 Class G,H,I,K, DLO, 2 PORT

Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

Specifications

Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper DLO Size Range	14 str.-6 str.
Conductor Size	14-4 AWG
Conductor - Copper Flex G Size Range	14 str.-6 str.
Conductor - Copper Flex K Size Range	14 str.-6 str.
Conductor - AL Str Size Range	14 AWG - 4 AWG
Conductor Type	- AL C Str-Size - CU C Str-Size - CU C Flex-Size
Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor - Copper Flex H Size Range	14 str.-6 str.
Conductor - Copper Flex I Size Range	14 str.-6 str.

Configuration

Number Of Ports	2
Connector Type	Multi Tap

Current

Operating Voltage	600 V
Voltage - Maximum	600 V

Dimensions

Package Height	0.000 in
Dimension - Height mm	31.75 mm
Dimension - Height inch	1.25 in
Package Weight	0.000 lb.
Dimension - Width mm	38.10 mm
Dimension - Width inch	1.50 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	27.44 mm
Dimension - Length Overall inch	1.08 in

General

Plated	Y
Trade Name	UNITAP™
UPC	621945440678
Insulation	Y
Hex Key	1/8 in
Material	Aluminum
Plating Type	Tin Plated
UPC 12 Digit	621945440678
UPC 14 Digit GTIN	00621945440678

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	100

Operational

Temperature Rating	135°C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)