




BS14, Vinyl Splice, #16-14 AWG

By Burndy
Catalog # [BS14](#)



Vinyl Splice For 16 - 14 AWG

Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion
- Expanded insulation support to lower inventory requirements
- Vinyl insulation provides an economical means of providing high dielectric values and cable insulation support

Application

For Accommodating A Broad Range Of 600 Volt Cables

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG-14 AWG

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.18 in
Dimension - Strip Length inch	1/4 in
Dimension - Diameter Max Size inch	0.18 in
Dimension - Length Overall inch	1.00 in

General

Insulation Type	Vinyl
Trade Name	VINYLINK™
Insulation	Y
Plated	Y
Color Code	Blue
Sub Brand	VINYLINK
UPC	781810805688
Type	BS
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810805688
UPC 14 Digit GTIN	00781810805688

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Operational

Temperature Rating	105
--------------------	-----

Product Assets

[Catalog \[English\]](#)