




BTCGC250SS, Aluminum Ground Tray Clamp, #6-250 kcmil

By Burndy
Catalog # [BTCGC250SS](#)

Aluminum ground tray clamp



Features

- Tin plated aluminum for durable, long lasting corrosion resistance
- cULus 467 Listed for Grounding and Bonding in US and Canada
- cULus 2703 Listed for solar PV applications in US and Canada
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation
- no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Grounding green hardware as required in Section 8.4 of UL2703

Application

Type BTCGC-SS clamps are suitable for outdoor applications and may be used with most types of cable tray with an inside or outside flange design

Specifications

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - AL Str Size Range	#6 AWG - 250 Kcmil
Conductor Range	#6 AWG - 250 Kcmil AL-CU
Conductor - Copper Str Size Range	6 AWG - 250 kcmil

Dimensions

Package Height	0.000 in
Length	2.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	2.43 in
Width	0.88 in
Thickness - Flange Plate	1/2 in
Allen Key Size	1/4 in
Dimensions	2.25 in x 0.88 in x 2.43 in

General

Material - Hardware	Stainless steel
UPC	621945505957
Material	Aluminum
Finish Type	Tin Plated

Logistics

Pallet Quantity	4800
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand