



CP2929, Heavy Duty Parallel Connector, Copper, A=250 kcmil, B=250 kcmil

By Burndy
Catalog # [CP2929](#)



Copper Alloy Heavy Duty Parallel Connector

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	250 kcmil
Conductor - Copper Str Size B	250 kcmil
Conductor - Copper Str Size A	250 kcmil
Range	
Conductor - Copper Str Size B	250 kcmil
Range	

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	4 in
Package Weight	0.000 lb.
Dimension - Width inch	2 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	4 in
Dimension - Width fraction	2 in

General

Plated	N
UPC	781810892008
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810892008
UPC 14 Digit GTIN	00781810892008

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)