



Substation - Aluminum Parallel Groove Clamp

By Burndy
Catalog # [CP39A39ASS](#)

Parallel Clamp



Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 700 kcmil • 715.5 kcmil • 750 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2
Conductor - AL Str Size Range	700 kcmil-715.5 kcmil
Conductor - ACSR Str Size	• 605 (26/7) kcmil • 636 (24/7) kcmil • 636 (26/7) kcmil • 605 (30/19) kcmil • 665.6 (24/7) kcmil • 636 (30/19) kcmil
Conductor - ACSR Str Size Range	605 (26/7) kcmil-665.6 (24/7) kcmil

Configuration

Connector Type	Spacer
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Height inch	3.32 in
Package Weight	0.000 lb.
Dimension - Width mm	76 mm
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	133.35 mm
Dimension - Length Overall inch	5.25 in

Force Related

Installation Torque Recommended in-lb	480 lb-in
---------------------------------------	-----------

General

Plated	N
Material - Hardware	Stainless Steel
UPC	781810499405
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810499405
UPC 14 Digit GTIN	00781810499405

Logistics

Minimum Pack Quantity	90
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)