



CT120200D0, Cable Tie, 120 Lb Tensile, Black

By Burndy
Catalog # [CT120200D0](#)

Nylon UNIRAP™ Cable Tie - 120 Lb. Tensile Strength

Features


- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	8 mm
Dimension - Width inch	0.3 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	221 mm
Dimension - Length Overall inch	8.70 in



Dimension - Bundle Diameter 2
Max inch

Force Related

Rating - Minimum Tensile 120
Strength lbs

General

Color	Black
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810333457
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810333457

Logistics

Minimum Pack Quantity	500
Carton Quantity	2500
Packaging Type	Bag

Operational

Operating Temperature Celcius 85 °C Max	
Operating Temperature Celcius -40 °C Min	

Product Assets

[Catalog \[English\]](#)



A Hubbell brand