




CT120300D0, Cable Tie, 120 Lb Tensile, Black

By Burndy
Catalog # CT120300D0



Nylon UNIRAP™ Cable Tie - 120 Lb. Tensile Strength

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Dimensions

Package Height	3.100 in
Package Weight	3.990 lb.
Dimension - Width mm	8 mm
Dimension - Width inch	0.3 in
Package Length	19.000 in
Package Width	13.000 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in
Dimension - Bundle Diameter Max inch	3

Force Related

Rating - Minimum Tensile Strength lbs	120
---------------------------------------	-----

General

Color	Black
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810333471
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810333471

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	2000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)



A Hubbell brand