



FD685T12CG2, Substation - Copper Stud Connector

By Burndy
Catalog # [FD685T12CG2](#)

Stud Connector, 2-1/4 IN Stud to 6 Holes NEMA Pad, Material: Cast Copper Alloy



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	2.25 in
Dimension - Height mm	0 mm
Dimension - Width inch	4.00 in
Dimension - B Length inch	2.69 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	8.62 in

General

Plated	N
Material - Hardware	Durium
UPC	621945010680
Type	Studs
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	621945010680
UPC 14 Digit GTIN	00621945010680

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)