



CT250600RQ0, Cable Tie, 250 Lb Tensile, UV Black, Releasable

By Burndy

Catalog # [CT250600RQ0](#)

Nylon UNIRAP™ Cable Tie - 250 Lb. Tensile Strength
(Releasable), 25 pack

Features

- Releasable Cable Tie
- Specially suitable for prototype construction or temporary installation
- Also suitable where service often requires adding or subtracting wires from an existing bundle

Application

For Use Where Service Requires Adding Or Subtracting Wires
From An Existing Wire Bundle

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - UV Rated	Yes
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Dimensions

Package Height	1.100 in
Package Weight	0.860 lb.
Package Length	31.000 in
Package Width	5.400 in
Dimension - L Length Overall mm	559 mm
Width	0.5 in
Length	23 in



Dimension - Width mm	13 mm
Dimension - Width inch	0.50 in
Dimension - Length Overall inch	22 in
Dimension - Bundle Diameter Max inch	6.00

Force Related

Rating - Minimum Tensile Strength lbs	250
---------------------------------------	-----

General

Trade Name	UNIRAP™
Color	Black
Sub Brand	UNIRAP,CABLE TIE
Series	UNIRAP™ Series
UPC	781810334850
Type	Heavy Duty Releasable
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810334850

Logistics

Minimum Pack Quantity	25
Pallet Quantity	9000
Carton Quantity	500

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)