



FD68ACG1, Substation - Aluminum Stud Connector

By Burndy
Catalog # [FD68ACG1](#)

Substation Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	2.000 in
Dimension - Pin Diameter fraction	2
Dimension - Pad Width inch	5.25 in
Package Height	0.000 in
Dimension - Height mm	83.3 mm
Dimension - Height inch	3.28 in
Package Weight	0.000 lb.

Dimension - Width mm	87 mm
Dimension - Width inch	3.44 in
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	171 mm
Dimension - B Length inch	2.50 in
Dimension - D inch	3.75 in
Dimension - N inch	0.88 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	6.75 in

General

Plated	N
Material - Hardware	Aluminum
UPC	621945144514
Material	Aluminum Alloy
Plating Type	Unplated
UPC 12 Digit	621945144514
UPC 14 Digit GTIN	00621945144514

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)