




CT50175M00, Tie, 1.87" Max Bundle, 50 Lb Tensile, UV Black

By Burndy
Catalog # [CT50175M00](#)



Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Certification - cULus	Yes
Certification - UV Rated	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
UL Listed	No
Certification - CSA Approved	No
Military Spec Number	MS3367-1-0
Certification - 94V0 Rated	N

Dimensions

Package Height	0.000 in
Length	7.56 in
Package Weight	0.000 lb.
Dimension - Width mm	5 mm
Dimension - Width inch	0.18 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	192 mm
Width	0.18 in

Dimension - Length Overall inch	7.56
Dimension - Bundle Diameter Max inch	1.875

Force Related

Rating - Minimum Tensile Strength lbs	50
---------------------------------------	----

General

Color	Black
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810332818
Material	Nylon 6/6
Military Specification	MS3367
UPC 14 Digit GTIN	00781810332818

Logistics

Minimum Pack Quantity	5000
Pallet Quantity	1
Carton Quantity	10000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)