




CT50175PMC, Tie, 1.87" Max Bundle,
Natural, Push Mount

By Burndy
Catalog # [CT50175PMC](#)

Nylon UNIRAP™ Cable Tie - 50 Lb. Tensile Strength (Push Mount), 100 pack

Features

- Push Mount Style

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UV Rated	No
UL Listed	No
Certification - CSA Approved	No
Certification - 94V0 Rated	N

Dimensions

Package Height	0.000 in
Length	7.99 in
Package Weight	0.000 lb.
Dimension - Width mm	5 mm
Dimension - Width inch	0.18 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	203 mm
Width	0.18 in
Dimension - Length Overall inch	7.99 in
Dimension - Bundle Diameter Max inch	1.87 in

Force Related

Rating - Minimum Tensile Strength lbs	50
---------------------------------------	----

General

Color	Natural
Trade Name	UNIRAP™
Series	UNIRAP™ Series
UPC	781810335048
Material	Nylon 6/6
UPC 14 Digit GTIN	00781810335048

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	1
Carton Quantity	1000
Packaging Type	Bag

Operational

Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)