



CTNT50275CO, Tie, 2.75" Max Bundle, Black, Nylon 12

By Burndy
Catalog # [CTNT50275CO](#)

Nylon 12 UNIRAP™ Cable Tie - 50 Lb. Tensile Strength

Features

- Nylon 12 Cable Ties provide excellent UV, chemical and moisture resistant
- Ties feature inside serrations and bent tail for quick, easy installation
- Smooth edge to prevent bundle damage
- Especially suitable in high moisture, corrosive (zinc chloride and dilute acids) environments
- Good in low temperatures
- Indoor/Outdoor applications

Application


Indoor and Outdoor mounting applications

Specifications

Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No

Dimensions

Package Height	0.900 in
Length	11 in
Thickness	0.06 in
Package Weight	0.380 lb.
Dimension - Width mm	4.8 mm
Dimension - Width inch	0.19 in
Package Length	16.250 in



Package Width	6.000 in
Dimension - L Length Overall	280 mm
Width	0.18 in
Dimension - Length Overall	11.00 in
inch	
Dimension - Bundle Diameter	2.75 in
Max inch	

Force Related

Tensile Strength	50 lb.
Rating - Minimum Tensile	50 lb
Strength lbs	

General

Color	Black
Trade Name	UNIRAP™
Sub Brand	UNIRAP
Series	UNIRAP™ Series
UPC	621945469433
Type	Cable Tie
Construction Material - Main	Nylon
Material	Nylon 12

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)