




DUW48, Deadend Clamp, Cast Copper Alloy

By Burndy
Catalog # [DUW48](#)



Cast Copper Alloy, Deadend Clamp, 1500 - 2000 kcmil, 4.14" Width

Features

- High strength, corrosion resistant copper alloy strain clamp
- Three silicon bronze U-bolts
- Single serrated saddle
- Galvanized steel clevis pin

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size Range	1500 kcmil-2000 kcmil
Conductor - Copper Str Size	• 1500 kcmil • 1600 kcmil • 1750 kcmil • 2000 kcmil

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Dimension - Height mm	94.5 mm
Dimension - Height inch	3.72 in
Dimension - Height fraction	3-18/25 in
Dimension - B Length fraction	5-14/25 in
Dimension - Width mm	105 mm
Dimension - Width inch	4.14 in
Dimension - L Length Overall mm	294 mm
Dimension - B Length inch	5.56 in
Dimension - Width fraction	4-7/50 in
Dimension - Length Overall inch	11.59 in

General

Plated	Y
Material - Hardware	Galvanized Steel
UPC	781810096956
Material	Copper Alloy
Plating Type	Tin - Electro Plated
UPC 14 Digit GTIN	00781810096956

Logistics

Minimum Pack Quantity	2
-----------------------	---

Product Assets

[Catalog \[English\]](#)