



Electric Hydraulic Pump, Air Bulb Control with Roll Cage, 10,000 psi

By Burndy
Catalog # [EPAC10](#)

EPAC Series, 1/2HP@3450 RPM 115VAC/60Hz



Features

- Roll cage
- 3-position switch and control box
- Air Bulb Actuator
- Full automatic or manual "Jog and Hold" cycles
- Oil level window
- 8-quart reservoir

Application

Pumping

Specifications

Standards - RoHS Compliance CM
Status

Current

Current Draw Max 10 Amperes

Dimensions

Length 18.5 in
Width 11.75 in
Weight 68 lb.

Height 17.5 in
Dimensions 18.5 in x 11.75 in x 17.5 in

General

Application - For Use On Use with 10,000 psi Remote Hydraulic Crimpers and Cutters Pump
Type 781810033371
UPC 12 Digit 00781810033371
UPC 14 Digit GTIN
Tool Type Pump, Electric Hydraulic
UPC 781810033371

Logistics

Package Contents Pump only
Minimum Pack Quantity 1

Operational

Power Source • 1/2 HP @ 3450 RPM, 115V-AC
 • 60 Hz Motor

Product Assets

[Catalog \[English\]](#)