



Electric/Hydraulic Pump Less Gage, 10,000 psi, 1/2 HP, 115V AC Motor

By Burndy
Catalog # [EPPI0ECLG](#)

EPP Series Pump, Less Gage, 1/2HP 115VAC



Features

- Small Electric Hydraulic Pump
- Remote Rocker Control Switch
- Operating Pressure: 10,000 psi
- 1/2 HP, 115 VAC Motor

Application

Pumping

Specifications

Standards - RoHS Compliance CM
Status

Current

Current Draw Max 12.5 Amperes

Dimensions

Length 16 in
Width 6 in
Weight 90.00 lb.
Height 8 in

Dimensions

16 in x 6 in x 8 in

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Type	Pump
UPC 12 Digit	781810046623
UPC 14 Digit GTIN	00781810046623
Tool Type	Pump, Electric Hydraulic
UPC	781810046623

Logistics

Package Contents	Pump only
Minimum Pack Quantity	1

Operational

Power Source	1/2 HP 115V-AC Motor
--------------	----------------------

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)