



FD68T12CG9, Substation - Copper Stud Connector

By Burndy
Catalog # [FD68T12CG9](#)

Stud Connector, 2 IN Stud to 4 Holes NEMA Pad, Material: Cast Copper Alloy

Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- Hex captured bolts provide one-wrench installation

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	2.00 in
Dimension - Pin Diameter fraction	2 in

Dimension - Height mm	0 mm
Dimension - Width inch	2.88 in
Dimension - B Length inch	2.69 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	6.56 in

Force Related

Installation Torque Recommended in-lb	360 lbs-in
---------------------------------------	------------

General

Plated	Y
Material - Hardware	Silicon Bronze
UPC	621945144569
Type	Studs
Material	Copper Alloy, Cast
Plating Type	Tin Plated
UPC 12 Digit	621945144569
UPC 14 Digit GTIN	00621945144569

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)