



EQC632C1, Transformer Grounding Connector

By Burndy
Catalog # EQC632C1

Transformer Grounding Connector



Features

- Equipment grounding connection point that installs within an equipment ground nut
- Fits all standard EEI-NEMA distribution transformers as a tank grounding terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	36.6 mm
Dimension - Height inch	1.44 in
Package Weight	0.000 lb.
Dimension - Width mm	23 mm
Dimension - Width inch	0.90 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.44 in
Dimension - Stud Size inch	25/64

Force Related

Installation Torque	240 LBS/in
Recommended in-lb	

General

Physical Attribute - Screw Type	Hexagonal Bolt
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810121009
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810121009
UPC 14 Digit GTIN	00781810121009

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)