



FCB634N, Substation - Copper Tap Adapter

By Burndy
Catalog # [FCB634N](#)

Transformer tap adapter, , Tin plated



Features

- Cast in one piece copper alloy
- Transformer tap adapter designed to accommodate NEMA drilled terminals taps from a single secondary transformer outlet
- Tin-Plated

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
----------------	---

Configuration

Physical Attribute - Number of Holes	4
Connector Type	T-Connector

Dimensions

Dimension - Pin Diameter inch	.50 in
Dimension - Pin Diameter fraction	1/2 in
Package Height	0.000 in
Dimension - Height mm	133.4 mm
Dimension - Height inch	5.25 in
Dimension - Height fraction	5-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	2.25 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in

General

Plated	Y
Sub Brand	XFMR CONN
UPC	781810002094
Type	T-Connector
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810002094
UPC 14 Digit GTIN	00781810002094

Logistics

Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)