



FD695TOCG1, Substation - Copper Stud Connector

By Burndy
Catalog # [FD695TOCG1](#)

Stud Connector, 70 mm Smooth Stud to 4 Holes NEMA Pad,
Material: Cast Copper Alloy

Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- Hex captured bolts provide one-wrench installation

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	2.750 in
-------------------------------	----------



Dimension - Height mm	0 mm
Dimension - Width inch	6.00 in
Dimension - B Length inch	3.25 in
Dimension - Length Overall inch	8.50 in

Force Related

Installation Torque	660 lbs-in
Recommended in-lb	

General

Plated	N
Material - Hardware	Silicon Bronze
UPC	621945144620
Type	Studs
Material	Copper Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	621945144620
UPC 14 Digit GTIN	00621945144620

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)