



FD72CG33, Substation - Copper Stud Connector

By Burndy
Catalog # [FD72CG33](#)

Copper Stud Connectors



Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- Hex captured bolts provide one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Connector Type	Stud Connector
----------------	----------------

Dimensions

Dimension - Pin Diameter inch	4.000 in
-------------------------------	----------

Dimension - Pin Diameter fraction	4 in
Dimension - Height mm	0 mm
Dimension - Bolt Size fraction	5/8
Dimension - B Length fraction	3-3/4 in
Dimension - L Length Overall mm	290 mm
Dimension - B Length inch	3.25 in
Dimension - Thread Size	5/8-12
Dimension - Threads per inch	12
Dimension - Length Overall inch	11.40 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810510117
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810510117
UPC 14 Digit GTIN	00781810510117

Logistics

Minimum Pack Quantity	12
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)