




FD65C6T14, Substation - Copper Stud Connector

By Burndy

Catalog # [FD65C6T14](#)

Cast Cu Alloy Substation Stud Connector, Bolted, Stud to Pad, 1"
- 14 Stud, 230 kV, Silicon Bronze H/W, 1075 Amp



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Connector Type	Stud Connector
----------------	----------------

Current

Amperage Rating	1075 A
-----------------	--------

Dimensions

Dimension - Pin Diameter inch	1.000 in
Dimension - Pin Diameter fraction	1 in

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	145 mm
Dimension - Thread Size	3/8-14
Dimension - Threads per inch	14
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.72 in

General

Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
UPC	781810003633
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810003633
UPC 14 Digit GTIN	00781810003633

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand