

FDA67T1213, Substation - Copper Stud Connector

By Burndy
Catalog # [FDA67T1213](#)



Copper Stud Connectors

Application

Substation

Specifications

Standards - RoHS Compliance UI
Status
Certification - CSA Approved No

Conductor

Conductor - Connection Stud to Bar
Combination

Configuration

Physical Attribute - Pad 90 Degree - horizontal
Orientation
Physical Attribute - Pad 3x2 - 4 holes
Configuration
Physical Attribute - Number of 4
Holes
Connector Type Stud Connector

Dimensions

Dimension - Pin Diameter inch 1.5 in
Dimension - Pin Diameter 1-1/2 in
fraction

Dimension - Pad Width inch 3.00 in
Dimension - Height mm 0 mm
Dimension - L Length Overall 84 mm
mm
Dimension - B Length inch 2.00 in
Dimension - D inch 2.00 in
Dimension - Threads per inch 12
Dimension - Length Overall 3.31 in
inch

General

Plated N
Material - Hardware DURIUM™ Silicon Bronze
UPC 621945144255
Type Studs
Material Copper Alloy
Plating Type Unplated
UPC 12 Digit 621945144255
UPC 14 Digit GTIN 00621945144255

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)