



FDA68G28, Substation - Copper Stud Connector

By Burndy
Catalog # [FDA68G28](#)

Copper Stud Connectors



Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	90 Degree - horizontal
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	2 in
-------------------------------	------

Dimension - Pin Diameter fraction	2 in
Dimension - Pad Width inch	3.94 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	243 mm
Dimension - D inch	3.94 in
Dimension - N inch	0.98 in
Dimension - Threads per inch	11
Dimension - Length Overall inch	9.57 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810368657
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810368657
UPC 14 Digit GTIN	00781810368657

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)