



FDR67B6J38OV, Substation - Copper Stud Connector

By Burndy
Catalog # [FDR67B6J38OV](#)

Copper Stud Connectors

Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- The pad is in a flag position to stud versus in-line

Application

Substation

Specifications

Standards - RoHS Compliance UI
Status

Conductor

Conductor - Connection Stud to Pad
Conductor - Connection Combination

Configuration

Physical Attribute - Pad Orientation 90 Degree - vertical
Physical Attribute - Pad Configuration 2x3.25 - 4 holes
Physical Attribute - Number of Holes 4
Connector Type Stud Connector



Dimensions

Dimension - Pin Diameter inch 1.500 in
Dimension - Pin Diameter fraction 1-1/2 in
Dimension - Pad Width inch 2.00 in
Dimension - Height mm 0 mm
Dimension - B Length fraction 2-9/50 in
Dimension - B Length inch 2.18 in
Dimension - D inch 3.25 in
Dimension - N inch 0.63 in
Dimension - Threads per inch 12

General

Plated N
Material - Hardware DURIUM™ Silicon Bronze
UPC 621945276086
Type Studs
Material Copper Alloy
Plating Type Unplated
UPC 12 Digit 621945276086
UPC 14 Digit GTIN 00621945276086

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)