



FD66D6W, Substation - Copper Stud Connector

By Burndy
Catalog # [FD66D6W](#)

Copper Stud Connectors

Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	In-line
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.250 in
Dimension - Pin Diameter fraction	1-1/4 in

Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	174 mm
Dimension - Thread Size	3/8-12
Dimension - Threads per inch	12
Dimension - Bolt Size fraction	3/8
Dimension - B Length inch	1.75 in
Dimension - D inch	4.00 in
Dimension - N inch	1.12 in
Dimension - Length Overall inch	6.84 in

General

Material - Hardware	DURIUM™ Silicon Bronze
Plated	Y
UPC	781810092705
Type	Studs
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810092705
UPC 14 Digit GTIN	00781810092705

Logistics

Minimum Pack Quantity	2
Pallet Quantity	432
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)