



FDR67T1212, Substation - Copper Stud Connector

By Burndy
Catalog # [FDR67T1212](#)

Copper Stud Connectors



Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- The pad is in a flag position to stud versus in-line

Application

Substation

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	90 Degree - vertical
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.500 in
-------------------------------	----------

Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pad Width inch	2.00 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	124 mm
Dimension - D inch	2.00 in
Dimension - Threads per inch	12
Dimension - Length Overall inch	4.88 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	621945201118
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	621945201118
UPC 14 Digit GTIN	00621945201118

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)