



FDR67T1215CG1, Substation - Copper Stud Connector

By Burndy
Catalog # [FDR67T1215CG1](#)

Stud Connector, 1-1/2" Stud (RUN), 3/4 x 5 CU Bar (Tap), Material: Cast Copper Alloy

Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- The pad is in a flag position to stud versus in-line

Application

Substation

Specifications

Standards - RoHS Compliance Status	UI
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Configuration

Physical Attribute - Pad Orientation	90 Degree - vertical
Connector Type	Stud Connector



Dimensions

Dimension - Pin Diameter inch	1.50 in
Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Height mm	0 mm
Dimension - Threads per inch	12
Dimension - Length Overall inch	7.50 in

General

Plated	Y
Material - Hardware	Durium
UPC	621945105317
Type	Studs
Material	Copper Alloy, Cast
Plating Type	Tin Plated Pad
UPC 12 Digit	621945105317
UPC 14 Digit GTIN	00621945105317

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)