



FDR70D16T0, Substation - Copper Stud Connector

By Burndy
Catalog # [FDR70D16T0](#)

Copper Stud Connectors



Features

- For use on stud to pads
- Allows for bolting cable and tubing terminals to equipment studs
- The pad is in a flag position to stud versus in-line

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection	Stud to Pad
Combination	

Configuration

Physical Attribute - Pad Orientation	90 Degree - vertical
Physical Attribute - Pad Configuration	4x4.25 - 4 holes
Physical Attribute - Number of Holes	4
Connector Type	Stud Connector

Dimensions

Dimension - Pin Diameter inch	3.000 in
-------------------------------	----------

Dimension - Pin Diameter fraction	3 in
Dimension - Pad Width inch	4.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	2-22/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	233 mm
Dimension - B Length inch	2.88 in
Dimension - D inch	4.25 in
Dimension - N inch	1.13 in
Dimension - Length Overall inch	9.18 in

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810171202
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810171202
UPC 14 Digit GTIN	00781810171202

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)