



Manual Hydraulic Foot Pumps, 10,000 psi, 1.12 Quarts Reservoir Volume

By Burndy
Catalog # [FP10](#)

Manual Hydraulic Foot Pump, 10000 psi



Features

- Diamond plate steel foot pad
- Long arm
- Spring loaded arm
- Built-in factory set pressure relief valve
- Quick disconnect hydraulic fitting
- Lightweight rugged design - portable
- Sturdy leg stabilizers

Application

Pumping

Specifications

Standards - RoHS Compliance CM
Status

Dimensions

Length 24.75 in
Width 5 in

Weight 19 lb.
Height 8 .00 in
Dimensions 24.75 in x 5 in x 8 .00 in

General

Application - For Use On Use with 10,000 psi Remote
Hydraulic Crimpers and Cutters
Type Pump
UPC 12 Digit 781810008324
UPC 14 Digit GTIN 00781810008324
Tool Type Pump, Manual Hydraulic
UPC 781810008324

Logistics

Package Contents Pump only
Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)