



GA25H26TN, Mech Ground Conn, Cu Cable to H-Beam, Tin Plated

By Burndy
Catalog # [GA25H26TN](#)

Mechanical Ground Connector for Copper Cable to "H" Beam

Features

- High copper alloy ground connector, Tin plated
- Joins wide range of cable parallel to "H" beams or square tube
- Silicon bronze for superior corrosion protection

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	4 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size	2/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm

Dimension - Height inch	4.75 in
Dimension - Height fraction	4-3/4 in
Package Weight	0.000 lb.
Dimension - Width mm	102 mm
Dimension - Width inch	4 in
Package Length	0.000 in
Package Width	0.000 in

Force Related

Installation Torque	240 Lb in
Recommended Run in-lb	

General

Plated	Y
UPC	781810562185
Material	Copper
Plating Type	Tin Plated
UPC 12 Digit	781810562185
UPC 14 Digit GTIN	00781810562185

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)