



FD67B6J0, Substation - Copper Stud Connector

By Burndy
Catalog # [FD67B6J0](#)

Copper Stud Connectors



Features

- High copper alloy stud connector allows bolting cable and tubing terminals to equipment studs
- Hex head captured bolts provide one-wrench installation
- One pad contact surface is on centerline of stud, pad is finished on both sides, all pads are 4-hole NEMA drilling

Application

Substation

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Conductor - Connection Stud to Pad
Combination

Configuration

Physical Attribute - Pad In-line
Orientation
Physical Attribute - Pad 2x3 - 2 holes
Configuration
Physical Attribute - Number of 2
Holes
Connector Type Stud Connector

Dimensions

Dimension - Pin Diameter inch	1.500 in
Dimension - Pin Diameter fraction	1-1/2 in
Dimension - Pad Width inch	2.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - D inch	3.00 in
Dimension - Threads per inch	12

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
UPC	781810376447
Type	Studs
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810376447
UPC 14 Digit GTIN	00781810376447

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)